

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

YZ-2R5556T

AWG8551

YZ-2R5556T

PAGE 1 OF 1

M

DRAWING
NUMBER

B

ISSUE

X115108-YZ

REPLACES

ECO-0005292

RELEASE NO.

CHECK

29 AUG 05

RJ

CHECK

06 MAY 04

AK

CHECK

06 MAY 04

AK

CHECK

06 MAY 04

AK

CHECK

06 MAY 04

AK

CHECK

06 MAY 04

AK


CHECK

06 MAY 04

RASTER

FO-52848-A

DRAWN




NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000±.002 CENTERS
- 2 - SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE-----8-15 OZ

RELEASE FORCE-----4 OZ MIN

DIFFERENTIAL TRAVEL-----.0004-.0025

OVERTRAVEL-----.005 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P N O

L96

15A 125, 250 OR 480 VAC
1/8 HP 125 VAC, 1/4 HP 250 VAC
1/2A 125 VDC, 1/4A 250 VDC

-L288-
-L306-
-L315-

CE

EN 05
EC

UL

16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

| | DIM. mm | TOL. mm/in | DIM. in | TOL. mm/in |
|--------------|------------|---------------|------------|---------------|
| NO PLACES | X | 1/64 | X | 0.003 |
| ONE PLACE | X.X | 0.4/0.015 | X.X | 0.003/0.015 |
| TWO PLACES | X.XX | 0.15/0.005 | X.XX | 0.003/0.015 |
| THREE PLACES | X.XXX | | X.XXX | 0.003/0.015 |
| ANGLES | | | | |

DESIGN UNITS

SI METRIC

US CUSTOMARY

WEIGHT .065 LB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[YZ-2R5556T](#)