

OPA-AR

([Home](#) : [Products](#) : [Sw itches](#) : [MICRO SWITCH™ Limit Sw itches](#) : [MICRO SWITCH™ Global Limit Sw itches](#) : [OP](#))



Enclosed Switch Series OP: Side Rotary, Fixed lever length with steel roller, 1NO 1NC Snap Action SPDT, CW actuation, High capacity

Actual product appearance may vary.

Product Specifications

| | |
|--------------------------------|--|
| Availability | Global |
| Operating Force (OF) | 3,34 N to 8,90 N [12 oz to 32 oz] |
| Release Force | 35,59 N [8 oz] min. |
| Pretravel (PT) | 5,56 mm [0.219 in] max. |
| Overtravel (OT) | 25° |
| Differential Travel (DT) | 0,3 mm [0.012 in] max. |
| Product Type | Enclosed Sw itches |
| Actuator | Side Rotary |
| Lever Type | 1.5 in Fixed Length Lever w ith back mounted Steel Roller (.75 in dia. x .25 in w ide) |
| Circuitry | 1NC 1NO Snap Action, SPDT |
| Ampere Rating | 20 A |
| Supply Voltage | 125 Vac, 250 Vac, 480 Vac |
| Housing Material | Aluminum Die-Cast |
| Termination Type | 0.5 in - 14NPT Conduit |
| Series Name | OP |
| Sealing | NEMA 1, 3, 4, 13 |
| UL File # | E12252 |
| Comment | CW actuation. High capacity. Field adjustable through 360 degrees. Roller lever may be positively locked at intervals of approx. 0.2 degrees |
| Agency Approvals and Standards | UL, CSA |
| UNSPSC Code | 39122213 |
| UNSPSC Commodity | 39122213 Limit Sw itches |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[OPA-AR](#)