

CLSXB4T

([Home](#) : [Products](#) : [Machine Safety](#) : [MICRO SWITCH™ Safety Sw itches](#) : [Cable Pull](#) : [CLSX](#))



CLSX Series, Explosion-proof Cable Pull Safety Sw itch, 1NC/1NO Direct Opening, Slow Action, Explosion-proof, 1/2 NPT, Silver Contacts

Actual product appearance may vary.

Product Specifications

Product Type	Cable Pull Safety Sw itch
Actuator	Cable, Maintained
Switch Type	1NC/1NO Direct Opening, Slow Action
Contact Material	Silver
Termination Type	1/2 NPT
Ampere Rating	100 mA to 10 A (Thermal)
Voltage	600 Vac and 250 Vdc max.
Housing Material	Zinc Die-Cast
Housing Type	Explosion-proof
Series Name	CLSX
Sealing	IP67; NEMA 1, 3, 4, 13
CSA File #	LR57326
UL File #	E37138, E157416
Agency Approvals and Standards	UL, CSA
Operating Temperature	-25 °C to 40 °C [-13 °F to 104 °F]
Availability	Global
UNSPSC Code	39122205
UNSPSC Commodity	39122205 Safety Sw itches
Indicator	None
Comment	IEC 947-5-1, EN60947-5-1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[CLSXB4T](#)