

BZG1-2RN8034

([Home](#) : [Products](#) : [Switches](#) : [MICRO SWITCH™ Limit Switches](#) : [MICRO SWITCH™ Medium-Duty Limit Switches](#) : [BZG/BZH](#))



Enclosed Switches Series BZG/BZH: Top Roller Plunger Actuator; 1NC 1NO SPDT Snap Action; 1/2 in - 14NPT conduit

Actual product appearance may vary.

Product Specifications

Availability	Global
Operating Force (OF)	4,17 N to 10,84 N [15 oz to 39 oz]
Release Force	2,78 N [10 oz] min.
Pretravel (PT)	1,98 mm [0.078 in] max.
Overtravel (OT)	5,56 mm [0.219 in] min.
Differential Travel (DT)	0,05 mm [0.002 in] max.
Product Type	Enclosed Switches
Actuator	Top Roller Plunger
Circuitry	1NC 1NO SPDT Snap Action
Ampere Rating	15 A Ind./0.5 A Res./0.25 A Res.
Supply Voltage	125 Vac, 250 Vac, or 480 Vac/125 Vdc/250 Vdc
Housing Material	Zinc Die-Cast
Housing Type	Split Housing, Side Mount
Series Name	BZG/BZH
Sealing	NEMA 1, 3, 4, 13
UL File #	E12252
Operating Temperature	-32 °C to 71 °C [-25 °F to 160 °F]
Comment	With seal boot on roller plunger
Agency Approvals and Standards	UL
UNSPSC Code	39122213
UNSPSC Commodity	39122213 Limit Switches
Sealed	Industrial

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZG1-2RN8034](#)