

BZG1-2RN234

([Home](#) : [Products](#) : [Sw itches](#) : [MICRO SWITCH™ Limit Sw itches](#) : [MICRO SWITCH™ Medium-Duty Limit Sw itches](#) : [BZG/BZH](#))



Enclosed Switches Series BZG/BZH: Top Roller Arm Actuator, Adjustable with Steel Roller; 1NC 1NO SPDT Snap Action; 1/2 in - 14NPT conduit

Actual product appearance may vary.

Product Specifications

Availability	Global
Operating Force (OF)	3,89 N to 7,23 N [14 oz to 26 oz]
Release Force	2,78 N [10 oz] min.
Pretravel (PT)	4,78 mm [0.188 in] max.
Overtravel (OT)	5,56 mm [0.219 in] min.
Differential Travel (DT)	0,15 mm [0.006 in] max.
Product Type	Enclosed Sw itches
Actuator	Top Roller Arm
Lever Type	Roller - Adjustable
Circuitry	1NC 1NO SPDT Snap Action
Ampere Rating	15 A Ind./0.5 A Res./0.25 A Res.
Supply Voltage	125 Vac, 250 Vac, or 480 Vac/125 Vdc/250 Vdc
Housing Material	Zinc Die-Cast
Housing Type	Split Housing, Side Mount
Series Name	BZG/BZH
Sealing	NEMA 1, 3, 4, 13
UL File #	E12252
Operating Temperature	-32 °C to 71 °C [-25 °F to 160 °F]
Comment	With seal boot on plunger; Lever field adjustable 360° horizontally and 250° vertically
Agency Approvals and Standards	UL
UNSPSC Code	39122213
UNSPSC Commodity	39122213 Limit Sw itches
Sealed	Industrial

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZG1-2RN234](#)