



1800-03G-K2N-B

( [Home](#) : [Products](#) : [Sensors](#) : [Pressure Sensors - Board Mount](#) : [Low Pressure Sensors](#) : [1800/1805](#) )

Image Not Available

1800/1805 Series, 0 psi to 15 psi pressure range, gage, 1.5 mA typ., 2mA max. supply current, TO-8 can

Actual product appearance may vary.

Product Specifications

Measurement Type	Gage
Pressure Range	0 psi to 15 psi
Supply Current	1.5 mA typ., 2.0 mA max.
Temperature Compensation	Yes
Top Side Overpressure	65 psi
Response Time	1 ms
Bottom Side Overpressure	45 psi
Package Type	TO-8 Can
Full Scale Span	38 mV to 42 mV
Insulation Resistance	100 mOhm at 50 Vdc
Repeatability	±0.0125 max. %FFS
Output Resistance	3.5 kOhm min., 6.0 kOhm max.
Common Mode Voltage	50% input
Shock	100 g for 11 ms
Vibration	10 g rms at 20 Hz to 200 Hz
Pressure Connection	3/16 in hole (top); none (bottom)
Operating Temperature	-40 °C to 121 °C [-40 °F to 257 °F]
Compensated Temperature Range	-1 °C to 54 °C [34 °F to 129 °F]
Media Compatibility	Clean, dry gases only.
UNSPSC Code	41111927
UNSPSC Commodity	41111927 Pressure Sensors
Life	100 million cycles
Availability	Global
Series Name	1800/1805

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1800-03G-K2N-B](#)