

364W500

([Home](#) : [Products](#) : [Sensors](#) : [Trimmers](#) : [364](#))



364 Series Trimmer, 500 Ohm, 0.5 W, 25 Turns, Square Body, Vertical Shaft

Actual product
appearance may vary.

Product Specifications

Product Type	Trimmer
Watts	0.5 W
Turns	25
Element Type	Cermet
Resistance Value	500 Ohm
Resistance Tolerance	± 10 %
Temperature Coefficient	± 100 ppm/ °C
Body	9,53 mm [0.375 in] square
Shaft Location	Vertical
Rotational Life	200 cycles
Series Name	364
Availability	Global
UNSPSC Code	32121616
UNSPSC Commodity	32121616 Trimmer resistor

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[364W500](#)