



SKU# 3570



Product Features:

Low profile design fits easily in small spaces
Adjustable time of delay for auto-off function
Compatible with Inspired LED products
Easy screw mount install

Specifications:

Net Weight- 32 grams
Max Load- 6 AMPs
Sensor Range- 8 meters
Working Temperature- (-20°) to (60°) C
12-24VDC screw terminal input/output

Works with plug-in power supplies only!



Instructions:

1. Secure LED lights in place according to their instructions
2. Strip ends of wire leading to LED lights
Note for Inspired LED Cables: white lettering indicates (+) side of wire
3. Match (+) and (-) polarity of wires to polarity of output screw terminals
4. Loosen output screw connections, insert wires, tighten screws to secure in place
5. Strip ends of wire leading to power source, match (+) and (-) polarity of wires to polarity of input screw terminal
6. Loosen input screw connections, insert wires, tighten screws to secure in place
7. Connect power source to test motion sensor

8. To adjust time of delay, insert screw driver into control dial located on the back of the device. Turn clockwise to increase length of time lights remain on, turn counterclockwise to decrease the time lights remain on before auto-off.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Inspired LED:](#)

[3570](#)