

**• Analog Product Family**

31 = Commercial/Industrial Analog
32 = Automotive Analog and Mixed Signal

• Product Type

AP = Audio Power Amplifier
BL = White LED Driver for LCD Backlight
FL = FxLED Driver
LT = Lighting LED Driver
SE = Sensor

• Temperature Grade

S1 = Commercial [0°C to 70°C]
S2 = Industrial temp. [-40°C to 85°C]
S3 = Industrial temp. [-40°C to 105°C]
S4 = Industrial temp. [-40°C to 125°C]
A1 = Automotive Grade [-40°C to +85°C]
A2 = Automotive Grade [-40°C to +105°C]
A3 = Automotive temp. [-40 to 125°C]

• Solder Type

Blank = Sn/Pb
L = Lead-free [RoHS Compliant]

• Package Type

C = WCSP
D = DFN
GR = SOP
QF = QFN
S = MSOP
SD = SOT89
ST = SOT23
TT = TSOT23
UT = UTQFN
Z = TSSOP

• Voltage Range / Parameters

Sense Voltage Range
V1 = 91mV to 101mV
V2 = 99mV to 110mV
Under-Voltage Range
V1 = 1.13V to 1.21V
V2 = 1.19V to 1.26V

• Package Option

Blank = Tray or Tube
TR = Tape & Reel

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ISSI:

[IS31AP4915-QFLS2-TR](#)