

Series 49 – ESD Resistant, Miniature Sealed, Lighted



Typical Applications

- Industrial equipment control handles
- Dog training control modules
- Outdoor controls
- Medical equipment



actual size



Ordering Information

Part Number	Body Style	Button Color	LED Color
49-111	Round Bezel	Black	–
49-112	Round Bezel	Red	–
49-113	Round Bezel	Green	–
49-114	Round Bezel	White	–
49-115	Round Bezel	Yellow	–
49-116	Round Bezel	Blue	–
49-211	Square Bezel	Black	–
49-212	Square Bezel	Red	–
49-213	Square Bezel	Green	–
49-214	Square Bezel	White	–
49-215	Square Bezel	Yellow	–
49-216	Square Bezel	Blue	–
49-411R	Illuminated Round	Black	Red
49-411G	Illuminated Round	Black	Green
49-412R	Illuminated Round	Red	Red
49-412G	Illuminated Round	Red	Green
49-413R	Illuminated Round	Green	Red
49-413G	Illuminated Round	Green	Green
49-9111	Snap-in	Black	–
49-9112	Snap-in	Red	–
49-9113	Snap-in	Green	–
49-9114	Snap-in	White	–
49-9115	Snap-in	Yellow	–
49-9116	Snap-in	Blue	–

Features

- Panel sealed IP67 (Front panel)
‘O’ ring and locknut are supplied
- Square or round bezels
- Illuminated and non-illuminated models
- Momentary action
- Thermoplastic case
- Gold-plated contacts
- ESD 15KV Min
- Threaded or snap-in cases

Electrical Characteristics

Circuitry	Current	Voltage
SPST-NO-DB	400mA	32 VAC Res
SPST-NO-DB	100mA	50 VDC Res
SPST-NO-DB	125mA	125 VAC Res

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ITW Switches:](#)

[49114](#)