# **PUSHBUTTON SWITCHES**

#### **12MM MINIATURE SEALED ELECTRO-MECHANICAL**

This rugged multi-option sealed pushbutton series offers the utmost in choices of mounting styles, colors, terminations, bezels, lighting and momentary or alternate-action switching. The Series 48 offers all these options in one compact package size.

## **APPLICATIONS**

- Office equipment
- Medical equipment
- Industrial machinery
- Outdoor controls
- Mass transportation
- Food processing equipment

## **KEY FEATURES:**

- Momentary or maintained action
- Gold contacts
- Many button colors
- Choice of LED colors (or non-lighted versions)

### **ORDERING INFORMATION:**

Switch Switch Module Mounting Voltage Function Termination **Bezel Type** LED Color<sup>†</sup> **Button Color** Resistor Туре Туре **RB** - Round, Black Momentary Solder Tabs 48-1 N - None RD - Red **B** - Bushing If Blank\* Maintained Solder Tabs 48-2 R - Red **GR** - Green 05 - 5V forward SB - Square, Black S - Snap-fit Momentary PC 48-5 RC - Round, Chrome BK - Black G - Green PC SC - Square, Chrome BL - Blue Maintained 48-6 Y - Yellow Momentary Wire Leads 48-A A - Amber YL - Yellow Maintained Wire Leads 48-B B - Blue **OR** - Orange W - White CR - Chrome RB - Red / Blue PK - Black with RG - Red / Green Standby Symbol WH - White 48-† Lighted switches come with wires on LEDs to protect from solder heat. \* Current limiting resistor is required to limit LED forward current to 20 mA **STANDARDS / AGENCY / RATINGS:** (not included). RoHS IP67

Solder, PC terminals or Wireleads

Panel sealed to IP 67

Long life






ACTUAL SIZE

www.itwswitches.com

# SERIES 48: 12MM MINIATURE SEALED ELECTRO-MECHANICAL

#### **PRODUCT DRAWINGS**



[MILLIMETERS] INCHES

3/13

Copyright © 2013 ITW Switches

Designs and specifications are subject to change without notice due to product improvement.

# MECHANICAL CHARACTERISTICS

**PUSHBUTTON SWITCHES** 

# CIRCUIT:

SPST-NO-DB (FORM X) BUTTON TRAVEL (NOM): [2.3] .09 OPERATING FORCE (NOM): [3N] 306g CONTACT BOUNCE (NOM): 1 ms PANEL THICKNESS: BUSHING MOUNTING: [0.5-3.0] .02-.12 SNAP-FIT MOUNTING: [1.3-3.0] .05-.12

**NUT TORQUE (MAX):** [11.5 kgf/cm] 10 lb/in

HARDWARE

BUSHING MOUNTING: BULK PACKAGED SEALING WASHER AND HEX NUT ARE INCLUDED.

#### **ENVIRONMENTAL SPECIFICATIONS**

ACTUATOR INGRESS PROTECTION: IP67

**OPERATING TEMPERATURE:** [-40 C to +85 C] -40 F to +185 F

#### **ELECTRICAL SPECIFICATIONS**

CURRENT RATING (resistive): 250mA @ 12VDC, 100K CYCLES 150mA @ 28VDC, 150K CYCLES (MOMENTARY)

100mA @ 48VDC, 100K CYCLES

10mA @ 12VDC, 1 MILLION CYCLES (MOMENTARY)

**DIELECTRIC STRENGTH:** 1.000 VAC

INSULATION RESISTANCE: 1G OHM

**CONTACT RESISTANCE:** 50m OHMS

WIRE LEADS:

UL STYLE 1007 26 AWG, STRANDED



800.544.3354

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

**ITW Switches**:

48-5RB-G-BK-B 48-3-RB-N-BK-B 48-2-RB-W-YL-B-05 48-A-SB-N-RD-B 48-2-RB-N-BK-S 48-1-RB-N-BL-S