




Technical drawing of a square flange with a central circular feature. The drawing includes dimension lines and labels:

- 注1** (Note 1) pointing to the central feature.
- 嵌合位置決り** (Position determined by fit) pointing to the outer edge of the central feature.
- 4-φT** (4 holes of diameter T) pointing to the four mounting holes.
- R** (radius) pointing to the outer edge of the flange.
- S** (thickness) pointing to the bottom edge.

Surface texture symbols are present on the top and bottom surfaces.



〔プレス・コンタクト〕

適用コネクタ品名		適用電線	
(上段)リール無. バラ		AWG. No	mm ²
(下段)リール付			
P (イン)	031-50465-010	#24~#20	0.2~0.5
	ST-GTC-16P1-3500		
	031-50466-010	#20~#16	0.5~1.25
	ST-GTC-16P2-3500		
S (アシン)	031-50467-010	#16~#14	1.25~2
	ST-GTC-16P3-3500		
	031-50468-010	#24~#20	0.2~0.5
	ST-GTC-16S1-3500		
T (アシン)	031-50469-010	#20~#16	0.5~1.25
	ST-GTC-16S2-3500		
	031-50470-010	#16~#14	1.25~2
	ST-GTC-16S3-3500		

注 1. 図示ノ位置ニ“社名”及“品名”ヲ表示スル。
但シ品名末尾ノ“FO-R”ハ表示シナイ。

2. コンタクトハ別売品デアル。(左表及下表参照)

3. リヤマウンティングノ場合、パネル厚サニ制限ガアリマス。(サラネジ使用)

4. インポート配列ハ承認図面(SJ019835)ヲ参照
13ト

〔マシンインタクト〕

適用コンタクト品名		適用電線 (mm ²)
P (ピン)	031-50721 (CONT-GTC16P-2)	0.3 ~ 0.5
	031-50723 (CONT-GTC16P-1)	0.75 ~ 1.5
	031-50599 (CONT-GTC16P)	1.25 ~ 2
S (ソケット)	031-50722 (CONT-GTC16S-2)	0.3 ~ 0.5
	031-50646 (CONT-GTC16S-1)	0.75 ~ 1.5
	031-50600 (CONT-GTC16S)	1.25 ~ 2

命名法

JL02-2A-米-B***C - F0 - R 特殊記号
コンタクト無し

コンタクトスタイル (P:ピン, S:ソケット)

インサート配列

シェルサイズ”

クラス

シエルタイフ°

シリーズ

4	コンタクト	銅合金	銀メッキ	—	インサート配列参照
3	インシュレータ	合成樹脂	ナシ	1	UL 94V-0 (色:黒)
2	リチエニングリング	リン青銅	亜金メッキ	1	黒色系干渉色
1	シールド	アルミ合金	亜金メッキ	1	黒色系干渉色
符号	名 称	材 料	仕 上	個 数	備 考

サイズ	A ネジ	M ^{+0.8}	K ^{+0.8}	N ^{-0.5}	R ^{+0.13}	S ^{+0.8}	T ^{+0.25} -0.13	0 ^{+0.5}	W ^{以下}
18	1 1/8-18UNEF-2A	19.1	2.7	24.9	26.97	34.9	3.05 3.1	30.2	3
20	1 1/4-18UNEF-	19.1	2.7	29.7	29.36	38.1	3.05 3.1	33.4	3
22	1 3/8-18UNEF-	19.1	2.7	32.1	31.75	41.3	3.05 3.1	36.6	3
24	1 1/2-18UNEF-	20.6	2.7	35.3	34.92	44.5	3.75 3.8	39.7	4.5
28	1 3/4-18UNS-	20.6	2.7	41.7	39.67	50.8	3.75 3.8	46.1	4.5
32	2-18UNS-	22.2	4.0	47.9	44.45	57.2	4.39 4.4	52.4	6
36	2 1/4-16UN-2A	22.2	4.0	54.3	49.23	63.5	4.39 4.4	58.3	6

特に指定のない限り、鋭い角やかえりは除去すること。 一般仕上		仕様書 T84-8 JACS-5060		第1版 2005.12.16	三角法	尺度	重量	個数	日本航空電子工業株式会社 昭島事業所 東京都昭島市中神町  この図面及びこの図面の関連資料は日本航空電子工業株式会社の承認がない限り製作及び写図を禁じます。
一般公差 特に指定がなければ CTS-4100 による		組立図番		製図 鈴木	担当 新田	名称 JL02-2A-＊- B＊＊C-F0-R			
寸法 角度 偏心量		材料		査閲 松本	承認 小野川	シリーズ JL02			
仕上 処理		シリアル		図番 S-1105736					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JAE Electronics:](#)

[JL02-2A-22-B14PC-F0-R](#) [JL02-2A-24-B28PC-F0-R](#) [JL02-2A-18-B1PC-F0-R](#) [JL02-2A-32-BA10SC-F0-R](#)