



SJ025426-E

DWG. NO.

SYM.	DCN NO.	DESCRIPTION	DATE	DRAWN	CHECKED	APP'D	APP'D



NOTE 1. CONTACTS ARE SUPPLIED IN REELED FORM WITH 3500 CONTACTS PER REEL.

NOTE 2. PART DESCRIPTION AND NUMBER OF CONTACTS OF A REEL ARE MARKED ON THE MAGAZINE AS SHOWN.

NOTE 3. A CRIMP TYPE IS MARKED AS INDICATED.

TABLE 1

CRIMP TYPE	APPLICABLE WIRE		DIMENSIONS
	WIRE SIZE	INSULATION OUTER DIA.	
C 1	AWG #14~16 (1.25mm~2mm)	φ 3.8 MAX.	3.7
C 2	AWG #16~20 (1.25mm~0.5mm)	φ 3.8 MAX.	3
C 3	AWG #20~24 (0.5mm~0.2mm)	φ 3.8 MAX.	2.2

NOTE 4. FOR AN INDIVIDUAL CONTACT, SEE DWG. NO. SJ025424.

DIMENSIONS ARE IN MILLIMETERS TOLERANCES ON: (INCHES)	
DIMENSION	ANGLES
. ±	X° ±
.X ±	X°X' ±
.XX ±	CONCENTRICITY
.XXX ±	WITHIN T. I. R.

3	#16 PIN CONTACT	3500	COPPER ALLOY	SILVER PLATING	
2	TAPE	1	PAPER		
1	MAGAZINE	1	PAPER		
ITEM	DESCRIPTION	Q'TY	MATERIAL	FINISH	REMARKS
REFERENCE DOCUMENT		DATE	SCALE	WT.	
		21. Apr. '95			
MATERIAL		DRAWN	JAE-CONNECTOR.COM Reference JAE		
		H. SAKURADA			
TREATMENT		CHECKED	TITLE		
		S. NANA O			
FINISH		APP'D	ST-JL05-16P -C*-3500 (MAGAZINE ASSEMBLY)		
		T. MORITA			
		APP'D	SERIES		
		M. Takagi			
			JL05		
			MUSASHINO, AKISHIMA-SHI TOKYO, JAPAN		
			DWG. NO.		
			SJ025426-E		

DOF-0-143

0 10 20 30 40 50 60 70 80 90 100

CDS-90-12057

SIZE A3

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JAE Electronics:](#)

[ST-JL05-16P-C1-3500](#) [ST-JL05-16P-C2-3500](#) [ST-JL05-16P-C3-3500](#)