




TABLE1. DIMENSION (NOTE.7)
表1. 寸法(注7)

NO. OF CONTACTS (n)	DIMENSIONS (mm)			
	a	b	c	d
30	8.89	20.925	16.525	11.67
40	12.065	24.1	19.7	14.845
60	18.415	30.45	26.05	21.195
80	24.765	36.8	32.4	27.545
90	27.94	39.975	35.575	30.72
100	31.115	43.15	38.75	33.895
120	37.465	49.5	45.1	40.245
140	43.815	55.85	51.45	46.595

SERIES シリーズ名	MA01	F	***	V	A	B	B
CONNECTOR TYPE F: FLOATING TYPE コネクタ タイプ F: フローティング タイプ							CH B 装 B
NUMBER OF CONTACTS 芯数							CON

MODIFY NUMBER
B:WITH BOSS
モイアイ番号
B:ボス有

CONNECTOR HEIGHT
B: STANDARD TYPE
製品高さ
B: 標準タイプ

CONTACT AREA GOLD PLATING THICKNESS
A: GOLD (0.1 μ m MIN)
接触部金メッキ厚
A: 金メッキ厚0.1 μ m以上

TERMINATION STYLE V:SMT、STRAIGHT TYPE、WITH HOLD DOWN
結線形態 V:SMT、ストレートタイプ、ホルト・ダウン有

NOTE 1. THE "MOVABLE INSULATOR" MOVES ± 0.5 mm IN THE X DIRECTION AND THE Y DIRECTION.

2. THERE IS A BOSS IN THE INSULATOR OF THIS PRODUCT.

3. THE COPLANARITY OF CONTACT AND HOLD DOWN SHALL BE 0.1 mm MAXIMUM.

4. PRODUCTION LOT NUMBER IS MARKED ON THE INSULATOR.

5. THE DIMENSION BETWEEN THE SUBSTRATE IS DEPEND ON COMBINATIONS OF CONNECTOR. REFER TO "JACS-11300"

6. IT IS RECOMMENDED TO USE AT LEAST 2 SPACERS MOUNTED DIAGONALLY ABOUT THE CONNECTOR TO FIX THE BOARDS. THE SPACERS SHOULD BE THE SAME HEIGHT AS THE DIMENSIONAL RANGE BETWEEN THE SUBSTRATES.

NOTE. 4 (EX.)
注. 4 (例)

 * 20 7 10 *

PRODUCTION DIVISION SETTING CODE	生産部門設定コード
----------------------------------	-----------

PRODUCT DAY (2 DIGITS NUMBER)
生産日(数字2桁)

MONTH (1 TO 9 FOR JAN. TO SEPT. RESPECTIVELY, OCT.=0 NOV.=X DEC.=Y)
生産月 (1月=1, 2月=2, ..., 10月=0, 11月=X, 12月=Y)

YEAR (LAST 2 DIGITS)
西暦年号の末尾2桁

MANUFACTURER CODE
組立部門識別コード

注 1.「可動インシュレータ」は、X方向、Y方向に各々±0.5mm可動する。
 2.本製品のインシュレータにはボスがある。
 3.定盤にのせた状態でコンタクト及びホルドダウンのコブラナリティは0.1mm以下とする。
 4.図示の位置にロット番号を表示する。
 5.基板間の寸法は、コンタクトの組合せによって異なる。「JACS-11300」参照願います。
 6.スベーパーをコンタクトの対角位置に2つ以上取付け、基板に固定する方法を推奨する。
 7.この場合スベーパーは、基板間の寸法7mm圏内で同一高さとする。

S/W

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JAE Electronics:](#)

[MA01F100VABBR300](#)