


JKL PART NO.: 2967-6G
 SOCKET COLOR: BLACK

WIRE TYPE: 20 AWG, BARE COPPER-7/28 STRAND (REF. GPT)
 WIRE COLOR: GREEN WITH WHITE TRACER

			<div>METRIC</div> <div></div> <div>THIRD ANGLE PROJECTION</div>		<div>DIMENSIONS ARE IN MILLIMETERS</div> <div>TOLERANCE UNLESS OTHERWISE SPECIFIED</div> <div>1 PL +/- 0.2</div> <div>2 PL +/- 0.20</div> <div>ANGLE +/-</div>		<div>JKL COMPONENTS CORPORATION</div> <div>TITLE</div> <div>T-1 1/2 WEDGE BASE LAMP SOCKET</div>									
B	DIM. MOL LEAD CHANGES		6/17/09		DRAWN BY		APP'D BY		DATE		SIZE	FSCM NO.	DRAWING NO.			
A	2 DIM. CHANGES TO REF.		12/31/03		L. WENGSTROM		L.R.		6/17/09		A	55335	SOCKET 2967-6G			
	RELEASED		10/22/02								SCALE		RELEASED	REVISION	REV.	SHEET
REV.	DESCRIPTION/ECO		APP'D		- CAD DRAWING -		MANUAL REVISIONS NOT PERMITTED		NONE				DATE	DATE	NO.	OF 1
NO.	NUMBER		DATE										10/22/02	6/17/09	B	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[2967-6G](#)