



JKL LAMP PART NUMBER	COLOR	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mA rms)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS)
BF20218-24B	LCD HIGH OUTPUT WHITE 8400°k RGB	1700 @ 0°C	740	5	38,000 ± 10%	20,000

* RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

			METRIC		DIMENSIONS ARE IN MILLIMETERS		JKL COMPONENTS CORPORATION	
					TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE	
			THIRD ANGLE PROJECTION		1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		MINIATURE COLD CATHODE FLUORESCENT LAMP	
			DRAWN BY		APPV'D BY DATE		SIZE FSCM NO. DRAWING NO.	
			L. WENGSTROM		L.W. 1/21/03		A 55335 BF20218-24B	
			- CAD DRAWING -		SCALE		RELEASED DATE	
			MANUAL REVISIONS NOT PERMITTED		NONE		11/4/02	
REV. NO.			DESCRIPTION/ECO NUMBER		APPV'D DATE		REVISION DATE	
							1/21/03	
							REV. NO. A SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[BF20218-24B](#)