


JKL LAMP PART NO.	COLOR LCD HIGH OUTPUT WHITE 8800°k RGB	STARTING CIRCUIT VOLTAGE VS (Vrms) @ 0°C	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mAmps)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS) AVERAGE
BF3294-24B	x = .285 y = .278	1550	620	5 ± 1	28,000 ± 10%	40,000

* RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0 2 PL +/- 0 ANGLE +/- 0		JKL COMPONENTS CORPORATION TITLE MINIATURE COLD CATHODE FLUORESCENT LAMP		
DRAWN BY L. WENGSTROM	APP'VD BY J.K.	DATE 8/5/04	SIZE A	FSCM NO. 55335	DRAWING NO. BF3294-24B	
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE NONE	RELEASED DATE 5/17/04	REVISION DATE 8/5/04	REV. NO. A	SHEET 1 OF 1

REV. NO.	DESCRIPTION/ECO NUMBER	APP'VD DATE
A	ELECTRICAL SPEC CHANGES	8/5/04
	RELEASE & CANCEL P-0308-05	5/17/04

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[329](#)