





JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
7112	5.0	.021	.034	0.43	10,000	C-2R
7114	5.0	.060	.050	0.63	100,000	C-2R
7118	5.0	.115	.150	1.89	40,000	C-2R

			METRIC  THIRD ANGLE PROJECTION	DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0	JKL COMPONENTS CORPORATION TITLE T-3/4 MICROMINIATURE BI-PIN BASED LAMPS				
B	REMOVE NOTES	1/3/22		DRAWN BY L. WENGSTROM	APPV'D BY SN	DATE 1/3/22	SIZE A	FSCM NO. 55335	DRAWING NO. BI-PIN T-3/4
A	CHANGE PIN MATERIAL NOTE	7/28/08							
	RELEASED - CANCEL SM-STDBP-T 3/4, 7810,	3/15/00							
	7111, BB23, 7113, 7115, 7116, 7119								
REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE	- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE NONE	RELEASED DATE 3/15/00	REVISION DATE 1/3/2022	REV. NO. B	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[7112](#) [7114](#) [7118](#)