






PC BOARD PUNCH PATTERN
(NO TREATMENT SUCH AS APPLICATION
OF FLUX, SHALL BE DONE.)

REV.	DESCRIPTION/ECO NO.	DATE
RELEASED		8/83
A	9.0 TO 9.0 MAX.	9/84
B	8.0 TO 8.0±0.1 AND 1.5±.05	1/85
C	TO 1.5±0.1	2/6/98
D	4.5 TO 4.5±0.1	1/1/00
DRAWING CONVERTED TO CAD-ADD LAMPS CNW1240.		
8111, CW11, CW145		
E	CNW1-7219 C-2F TO C-2V	7/12/00
F	DEGREE DIM. CORRECT. TO 3/14/01	
PC PATTERN		

JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	*MSCP ±25%	*LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
CNW1-8732	2.5	.100	.100	1.25	10,000	C-2R
CNW1-CW27	5.0	.040	.028	0.35	20,000	C-2R
CNW1-683	5.0	.060	.050	0.63	100,000	C-2R
CNW1-715	5.0	.115	.150	1.89	40,000	C-2R
CNW1-7218	10.0	.027	.100	1.26	10,000	C-2F
CNW1-CW44	12.0	.040	.090	1.13	10,000	C-2F
CNW1-7219	12.0	.060	.150	1.89	16,000	C-2V
CNW1-CW1240	14.0	.040	.120	1.51	16,000	C-2F
CNW1-23	14.0	.040	.150	1.89	16,000	C-2F
CNW1-8111	14.0	.065	.150	1.89	16,000	C-2F
CNW1-CW11	14.0	.065	.200	2.51	10,000	C-2F
CNW1-CW145	14.5	.030	.080	1.00	5,000	C-2F
CNW1-7220	18.0	.026	.150	1.89	16,000	C-2F
CNW1-6838	28.0	.024	.150	1.89	16,000	CC-2F

*LAMP RATED ONLY WITHOUT BASE

METRIC	DIMENSIONS ARE IN MILLIMETERS	TOLERANCE UNLESS OTHERWISE SPECIFIED
	1 PL. +/- .02	2 PL. +/- .020
THIRD ANGLE PROJECTION	ANGLE +/- .0	
DRAWN BY L. WENGSTROM	APPROVED BY E. D.	DATE 3/14/01
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		
TITLE T-1 NEO-WEDGE BASE WITH MULTIPLE LAMP LISTING		
SCALE NONE	SIZE A	FIG. NO. 55335
DRAWING NO. CNW1-MULTI		REV. NO. F
RELEASED DATE 8/83	REVISION DATE 3/14/01	SHEET 1 OF 1

JKL COMPONENTS CORPORATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

JKL Components:

[CNW1-23](#) [CNW1-6838](#) [CNW1-7219](#) [CNW1-8111](#)