


JKL LAMP NUMBER	VOLTS RATED	WATTS	INITIAL MSCP	INITIAL LUMENS	AVERAGE LIFE HRS.	FILAMENT TYPE
6S6-120-DCB	120	6	3.18	40.0	1,500	C-7A
6S6-145V-DCB	145	6	3.18	40.0	1,500	C-7A
10S6-230V-DCB	230	10	5.97	75.0	1,500	C-1

METRIC



THIRD ANGLE PROJECTION

DRAWN BY
L. WENGSTROM

DIMENSIONS ARE IN MILLIMETERS

TOLERANCE UNLESS OTHERWISE SPECIFIED

1 PL +/- 0.2
2 PL +/- 0.20
ANGLE +/- 0

APPV'D BY DATE
QC 3/1/01

JKL

COMPONENTS CORPORATION

TITLE

S-6 DOUBLE CONTACT BAYONET BASE LAMP

SIZE

A

FSCM NO.

55335

DRAWING NO.

BAYONET DOUBLE CONTACT S-6

SCALE

NONE

RELEASED DATE

3/1/01

REVISION DATE

REV. NO.

SHEET

1 OF 1

REV. NO.

DESCRIPTION/ECO NUMBER

APPV'D DATE

- CAD DRAWING -

MANUAL REVISIONS NOT PERMITTED

RELEASED AS CAD

3/1/01

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[6S6-120V-DCB](#) [6S6-145V-DCB](#)