



JKL LAMP NUMBER	VOLTS RATED	AMPS $\pm 10\%$	MSCP $\pm 25\%$	LUMENS $\pm 25\%$	AVERAGE LIFE HRS.	FILAMENT TYPE
1493	6.5	2.75	23.0	289.1	100	C-6
94	12.8	1.04	15.0	188.6	700	C-6
306	28.0	.51	15.0	188.6	300	*C-2V
1692	28.0	.61	15.0	188.6	1,000	2C-2R
895	40.0	.53	14.0	176.0	3,800	*C-2V

* SUPPORTED

METRIC THIRD ANGLE PROJECTION			DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		JKL COMPONENTS CORPORATION					
					TITLE S-8 DOUBLE CONTACT BAYONET BASE LAMP					
DRAWN BY L. WENGSTROM			APPVD BY J.K.		DATE 7/21/05		SIZE A		FSCM NO. 55335	DRAWING NO. BAYONET DOUBLE CONTACT S-8
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE NONE		RELEASED DATE 5/9/01		REVISION DATE 7/21/05		REV. NO. A	SHEET 1 OF 1

REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE
A	DELETE CANCELLED PART NO. 1130 RELEASED AS CAD	7/21/05 5/9/01

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[895](#) [2232SB](#)