



JKL LAMP NUMBER	VOLTS RATED	AMPS $\pm 10\%$	MSCP $\pm 25\%$	LUMENS $\pm 25\%$	AVERAGE LIFE HRS.	FILAMENT TYPE AND POSITION
1034	12.8 14.0	1.80 .59	32.0 3.0	402.2 37.7	200 5,000	C-2R POSITION #2 = 2 FILAMENTS C-2R POSITION #1 = 1 FILAMENT
1157	12.8 14.0	2.10 .59	32.0 3.0	402.2 37.7	1,200 3,000	C-2R POSITION #2 = 2 FILAMENTS C-2R POSITION #1 = 1 FILAMENT

METRIC		DIMENSIONS ARE IN MILLIMETERS		JKL COMPONENTS CORPORATION			
 THIRD ANGLE PROJECTION		TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		TITLE			
				S-8 DOUBLE CONTACT INDEX BAYONET BASE LAMP			
DRAWN BY		APPVD BY		DATE	SIZE	FSCM NO.	DRAWING NO.
L. WENGSTROM		QC		5/18/01	A	55335	BAYONET DOUBLE CONTACT INDEX S-8
- CAD DRAWING -		SCALE		RELEASED DATE	REVISION DATE	REV. NO.	SHEET
MANUAL REVISIONS NOT PERMITTED		NONE		5/9/01	5/18/01	A	1 OF 1

REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE
A	DIM. CHNG ON CONTACTS TO 6.48/7.08 RELEASED AS CAD	5/18/01 5/9/01

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[1157](#)