


JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
E14140*	14.0	.140	.630	8.00	5,000 D.C.	C-2V

\*PRODUCTION CHANGE TO Pb FREE GLASS, CONTACT JKL FOR LOT IDENTIFICATION.

			<b>METRIC</b>  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		<b>JKL COMPONENTS CORPORATION</b>			
			DRAWN BY		APPV'D BY DATE		TITLE <b>T-1 1/2 STANDARD GLASS WEDGE BASE</b>			
			L. WENGSTROM		J.K. 8/27/04		SIZE	FSCM NO.	DRAWING NO.	E14140
A Pb FREE NOTE ADDED RELEASED - CANCEL P-0007-07			8/27/04		7/25/00					
REV. NO.	DESCRIPTION/ECO NUMBER		APPV'D DATE	- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE	NONE	RELEASED DATE	7/25/00
							REVISION DATE	8/27/04	REV. NO.	A
									SHEET	1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[E14140](#)