


| JKL LAMP NUMBER | VOLTS RATED | AMPS ±10% | MSCP ±25% | LUMENS ±25% | AVERAGE LIFE HRS. | FILAMENT TYPE |
|--------------------|----------------|--------------|--------------|----------------|----------------------|------------------|
| 27 | 4.9 | .300 | 1.40 | 17.60 | 30 | C-2R |
| 425 | 5.0 | .500 | 2.30 | 28.91 | 15 | C-2R |
| 605 | 6.15 | .500 | 3.40 | 42.74 | 15 | C-2R |

METRIC



THIRD ANGLE
PROJECTION

DIMENSIONS ARE
IN MILLIMETERS

TOLERANCE UNLESS
OTHERWISE SPECIFIED

1 PL +/- 0.2
2 PL +/- 0.20
ANGLE +/- 0

DRAWN BY
L. WENGSTROM

APPV'D BY DATE
QC 2/27/01

JKL

COMPONENTS CORPORATION

TITLE

G-4 1/2 MINIATURE SCREW BASE

- CAD DRAWING -

MANUAL REVISIONS NOT PERMITTED

SIZE
A

FSCM NO.
55335

DRAWING
NO.

SCREW BASE G-4 1/2

SCALE

NONE

RELEASED
DATE

2/27/01

REVISION
DATE

REV.
NO.

SHEET
1 OF 1

REV.
NO.

DESCRIPTION/ECO
NUMBER

APPV'D
DATE

RELEASE

2/27/01

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[425](#) [605](#)