



NOTE:
 THREAD 5/16"-32 NEF-2
 PITCH DIA. .2922" +.0000/-.0033

JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
323	3.0	.190	.250	3.14	350	C-2R
8553	6.3	.200	.550	6.91	5,000	C-2R
8623	28.0	.040	.340	4.27	2,800	C-2F

METRIC THIRD ANGLE PROJECTION	DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0	JKL COMPONENTS CORPORATION	
	TITLE T-1 1/4 KNURL SCREW BASE		
DRAWN BY L. WENGSTROM	APPVD BY QC	DATE 10/13/00	SIZE A
FSCM NO. 55335		DRAWING NO. SCREW BASE KNURL T-1 1/4	
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE NONE	RELEASED DATE 10/13/00
REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE	REV. NO.
		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[8623](#) [323](#) [8553](#)