



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
51	7.5	.220	1.00	12.57	1,000	C-2R
53	14.4	.120	1.00	12.57	1,000	C-2V
1445	14.4	.135	.70	8.80	2,000	C-2V
	18.0	.150	1.50	18.86	250	
1450	24.0	.035	.23	2.89	3,000	C-2F
356	28.0	.170	3.50	44.00	500	C-2F

			<b>METRIC</b>  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		<b>JKL COMPONENTS CORPORATION</b> TITLE <b>G-3 1/2 SINGLE CONTACT BAYONET BASE LAMP</b>				
DRAWN BY L. WENGSTROM			APPV'D BY QC		DATE 3/8/01		SIZE <b>A</b>	FSCM NO. <b>55335</b>	DRAWING NO. <b>BAYONET SINGLE CONTACT G-3 1/2</b>		
RELEASED AS CAD			3/8/01		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE <b>NONE</b>	RELEASED DATE <b>3/8/01</b>	REVISION DATE	REV. NO.	SHEET <b>1 OF 1</b>
REV. NO.	DESCRIPTION/ECO NUMBER		APPV'D DATE								

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[51](#) [1445](#)