


JKL LAMP NUMBER	VOLTS RATED	AMPS $\pm 10\%$	*MSCP $\pm 25\%$	*LUMENS $\pm 25\%$	AVERAGE LIFE HRS.	FILAMENT TYPE
81	6.5	1.02	6.00	75.42	500	C-2R
89	13.0	.58	6.00	75.42	750	C-2R
67	13.5	.59	4.00	50.28	5,000	C-2R
1251	28.0	.23	3.00	37.71	2,000	2C-2V
303	28.0	.30	6.00	75.42	500	C-2F
623	28.0	.37	6.00	75.42	1,000	2C-2V

\*LAMP RATED ONLY WITHOUT BASE.

<b>METRIC</b>  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		<b>JKL COMPONENTS CORPORATION</b> TITLE <b>G-6 SINGLE CONTACT BAYONET BASE LAMP</b>			
DRAWN BY L. WENGSTROM		APPV'D BY DATE QC 3/26/01		SIZE <b>A</b>	FSCM NO. <b>55335</b>	DRAWING NO. <b>BAYONET SINGLE CONTACT G-6</b>	
RELEASED AS CAD 3/26/01		APPV'D DATE 3/26/01		SCALE <b>NONE</b>		RELEASED DATE 3/26/01	
REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE	- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		REVISION DATE	REV. NO.	
					SHEET <b>1 OF 1</b>		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[89](#) [67](#)