



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	*MSCP ±25%	*LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
89	13.0	.58	6.00	75.42	750	C-2R
67	13.5	.59	4.00	50.28	5,000	C-2R
1251	28.0	.23	3.00	37.71	2,000	2C-2V
303	28.0	.30	6.00	75.42	500	C-2F
623	28.0	.37	6.00	75.42	1,000	2C-2V

*LAMP RATED ONLY WITHOUT BASE.

METRIC THIRD ANGLE PROJECTION			DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		JKL COMPONENTS CORPORATION				
					TITLE G-6 SINGLE CONTACT BAYONET BASE LAMP				
DRAWN BY L. WENGSTROM			APPVD BY DATE J.K. 7/21/05		SIZE A	FSCM NO. 55335	DRAWING NO. BAYONET SINGLE CONTACT G-6		
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE NONE		RELEASED DATE 3/26/01	REVISION DATE 7/21/05	REV. NO. A	SHEET 1 OF 1	

REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE
A	DELETE PART NO. 81 RELEASED AS CAD	7/21/05 3/26/01

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[623](#)