


JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
7637	3.0	.190	.250	3.14	350	C-2R
7583	5.0	.060	.050	0.63	100,00	C-2R
7515	5.0	.115	.150	1.89	40,000	C-2R
7628	6.0	.200	.630	7.92	1,000	C-2R
DB21	14.0	.060	.200	2.51	10,000	C-2V
7646	14.0	.080	.500	6.29	2,500	C-2F
7632	28.0	.040	.320	4.02	2,800	C-2F

#### NOTES:

1. GLASS ENVELOPE TO BE TIPLESS AND SEAMLESS.
2. BASE MATERIAL: NYLON OR EQUIVALENT.
3. BASE COLOR: WHITE.
4. PIN MATERIAL: NICKEL WIRE, GOLD PLATED.
5. LAMPS TO BE 100% AGED FOR AN EQUIVALENT TO A MINIMUM OF TEN HOURS AT RATED VOLTAGES.
6. FINAL INSPECTION ON ALL LAMPS TO BE PER: MIL. STD. 105E TO AN AQL OF 2.5.
7. DIMENSIONS NOT PROVIDING TOLERANCES ARE REFERENCE DIMENSIONS ONLY.

			<b>METRIC</b>  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		<b>JKL COMPONENTS CORPORATION</b>			
			DRAWN BY L. WENGSTROM		APPV'D BY DATE BW 3/9/00		TITLE <b>T-1 1/4 STANDARD BI-PIN BASED LAMPS</b>			
RELEASED - CANCEL SM-STDBP-T 1 1/4, DB90, DB91, 7310, DB09, DB44, DB48, DB07, DB40			3/9/00		SIZE <b>A</b>		FSCM NO. <b>55335</b>		DRAWING NO. <b>BI-PIN T-1 1/4</b>	
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE NONE		RELEASED DATE 3/9/00		REVISION DATE		REV. NO. SHEET 1 OF 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[7646](#) [7515](#) [7583](#)