


JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
2	5.0	.021	.034	0.43	10,000	C-2R
6803	5.0	.060	.030	0.38	100,000	C-2R
6833	5.0	.060	.050	0.63	100,000	C-2R
7133	5.0	.075	.090	1.13	25,000	C-2R
7153	5.0	.115	.150	1.89	40,000	C-2R
BW79	6.0	.065	.110	1.40	10,000	C-2R

NOTES:

- GLASS ENVELOPE TO BE TIPLESS AND SEAMLESS CONSTRUCTION TO PROVIDE UNDISTORTED END VIEWING.
- WIRE TERMINALS TO BE TINNED DUMET TYPE WIRE. OPTIONAL PLATING MATERIALS ARE AVAILABLE.
- ALL LAMPS TO BE 100% AGED FOR AN EQUIVALENT OF TEN HOURS OF THE RATED VOLTAGES.
- FINAL INSPECTION ON ALL LAMPS TO BE PER MIL. STD. 105D TO AN AQL OF 2.5.
NOTE: AS15 TYPE LAMPS WILL BE 100% INSPECTED FOR AMPERAGE AND MSCP RATINGS.
- ALL DIMENSIONS PROVIDED HEREIN, NOT LISTING TOLERANCES, ARE CONSIDERED REFERENCE DIMENSIONS ONLY.

			<div>METRIC</div> <div></div> <div>THIRD ANGLE PROJECTION</div>		<div>DIMENSIONS ARE IN MILLIMETERS</div> <div>TOLERANCE UNLESS OTHERWISE SPECIFIED</div> <div>1 PL +/- 0.2</div> <div>2 PL +/- 0</div> <div>ANGLE +/- 0</div>		<div>JKL COMPONENTS CORPORATION</div> <div>TITLE</div> <div>T-3/4 STANDARD WIRE TERMINAL LAMP</div>							
C	LEAD DIA. CHNG TO Ø0.2 REF.		02/08/00		DRAWN BY		APPV'D BY DATE		SIZE	FSCM NO.	DRAWING NO.	WIRE TERMINAL T-3/4		
B	CORRECTION ON REV. LAMP LIST		01/28/00		L. WENGSTROM		BW 02/08/00		A	55335				
A	DRAWING CONVERTED TO CAD-LAMPS 7100, 8534, BW23,6153, 8666, 7102 DELETED		01/17/00						SCALE		RELEASED DATE	REVISION DATE	REV. NO.	SHEET
	RELEASED		12/84						NONE		12/84	02/08/00	C	1 OF 1
REV. NO.	DESCRIPTION/ECO NUMBER		APPV'D DATE		- CAD DRAWING -									
MANUAL REVISIONS NOT PERMITTED														

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[6803](#)