


**NOTES:**

1. GLASS ENVELOPE TO BE TIPLESS AND SEAMLESS.
2. BASE MATERIAL: BRASS, NICKEL PLATED.
3. LAMPS TO BE 100% AGED FOR EQUIVALENT OF TEN HOURS AT RATED VOLTAGE.
4. LAMPS TO BE DIESUNK WITH "JKL" AND NUMBER (EX: JKL 8270).
5. FINAL INSPECTION PER MIL. STD. 105D TO AN AQL OF 2.5 (NOTE: AS15 AND AS10 LAMPS WILL BE 100% INSPECTED FOR MSCP AND AMPERAGE).

JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
8270	5.0	.115	.150	1.89	40,000	C-2R

<b>METRIC</b>  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		<b>JKL COMPONENTS CORPORATION</b>			
DRAWN BY L. WENGSTROM		APPVD BY DATE BW 4/4/00		SIZE <b>A</b> SCALE <b>NONE</b>		FSCM NO. <b>55335</b> DRAWING NO.	
RELEASE & CANCEL 7122, 8913, 6183, 8828 4/4/00		APPVD DATE		TITLE <b>T-3/4 STANDARD MICRO MIDGET FLANGE</b>		<b>FLANGE T-3/4</b>	
REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE	- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		RELEASED DATE <b>4/4/00</b>	REVISION DATE REV. NO.	
					SHEET <b>1 OF 1</b>		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[8270](#)