


JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	*MSCP ±25%	*LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
6MB	6.0	.140	.12	1.51	20,000	C-2F
24MB	24.0	.073	.50	6.29	10,000	C-2F
28MB	28.0	.040	.29	3.65	5,000	C-2F
48MB	48.0	.053	.70	8.80	10,000	C-7A
60MB	60.0	.050	.73	9.18	7,500	C-2F
120MB	120.0	.025	.32	4.02	10,000	CC-7A

*LAMP RATED ONLY WITHOUT BASE.

METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		JKL COMPONENTS CORPORATION			
DRAWN BY L. WENGSTROM		APPVD BY DATE QC 10/11/00		SIZE A	FSCM NO. 55335	DRAWING NO. TELEPHONE BAYONET T-2 1/2	
RELEASED AND CANCEL 12MB 10/11/00		APPVD DATE 10/11/00		SCALE NONE		RELEASED DATE 10/11/00	
REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE	- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		REVISION DATE	REV. NO.	
					SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

JKL Components:

[24MB](#) [60MB](#) [6MB](#) [48MB](#) [28MB](#)