




## FEATURES

G4 Base - Non-Polarized


Wide Input Voltage Range

Low Power Usage

Omni Directional Light Distribution

Efficacy of 47Lm/Watt

| VOLTAGE<br>AC/DC |     |     | WATTS |     |     | ILLUMINANCE<br>FLUX<br>lm TYP | COLOR<br>DEGREE K |
|------------------|-----|-----|-------|-----|-----|-------------------------------|-------------------|
| MIN              | NOM | MAX | MIN   | NOM | MAX |                               |                   |
| 8                | 12  | 30  | 1.2   | 1.4 | 1.6 | 75                            | 3500              |

|                                                                                                                                                        |  |                                                                                                                                                          |                                   |                                                                                       |                                            |                                             |                                 |                                    |  |
|--------------------------------------------------------------------------------------------------------------------------------------------------------|--|----------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|---------------------------------------------------------------------------------------|--------------------------------------------|---------------------------------------------|---------------------------------|------------------------------------|--|
| <div>METRIC</div> <div></div> <div>THIRD ANGLE<br/>PROJECTION</div> |  | <div>DIMENSIONS ARE<br/>IN MILLIMETERS</div> <div>TOLERANCE UNLESS<br/>OTHERWISE SPECIFIED</div> <div>1 PL +/- 0.2<br/>2 PL +/- 0.20<br/>ANGLE +/-</div> |                                   | <div>JKL COMPONENTS CORPORATION</div> <div>TITLE</div> <div>MULTI CHIP LED LAMP</div> |                                            |                                             |                                 |                                    |  |
| <div>DRAWN BY</div> <div>L. WENGSTROM</div>                                                                                                            |  | <div>APPV'D BY</div> <div>L.R.</div>                                                                                                                     | <div>DATE</div> <div>5/9/12</div> | <div>SIZE</div> <div>A</div>                                                          | <div>FSCM NO.</div> <div>55335</div>       | <div>DRAWING NO.</div> <div>Z-G4-15WW</div> |                                 |                                    |  |
| <div>- CAD DRAWING -</div> <div>MANUAL REVISIONS NOT PERMITTED</div>                                                                                   |  |                                                                                                                                                          |                                   | <div>SCALE</div> <div>NONE</div>                                                      | <div>RELEASED DATE</div> <div>5/9/12</div> | <div>REVISION DATE</div> <div></div>        | <div>REV. NO.</div> <div></div> | <div>SHEET</div> <div>1 OF 1</div> |  |

|          |                              |             |
|----------|------------------------------|-------------|
| REV. NO. | DESCRIPTION/ECO NUMBER       | APPV'D DATE |
|          | RELEASED & CANCEL PL-0912-01 | 5/9/12      |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[Z-G4-15WW](#)