



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
E6522	6.0	.030	.025	0.31	10,000	C-2V
E79	6.0	.200	.600	7.54	1,000	C-2R
E84	6.3	.040	.030	0.38	20,000	C-2V
E86	6.3	.200	.400	5.03	20,000	C-2V
E12522	12.0	.030	.045	0.57	10,000	C-2F
E21203A	12.0	.100	.640	8.04	2,000	C-2V
E73	14.0	.080	.300	3.77	15,000	C-2V
E37	14.0	.090	.500	6.29	1,500	C-2F
E74*	14.0	.100	.720	9.05	1,000	C-2V
E13522	24.0	.030	.160	2.01	5,000	C-2F
E85	28.0	.040	.300	3.77	10,000	C-2F
E17	28.0	.065	.650	8.17	5,000	C-2F

\*PRODUCTION CHANGE TO Pb FREE GLASS, CONTACT JKL FOR LOT IDENTIFICATION.

		<b>METRIC</b> DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0													
		<b>TITLE</b> T-1 1/2 STANDARD GLASS WEDGE BASE													
<b>REV. NO.</b> A Pb FREE NOTE ADDED RELEASED & CANCEL GW-STD-T1 1/2		<b>DATE</b> 8/25/04 5/5/00		<b>DRAWN BY</b> L. WENGSTROM		<b>APPV'D BY</b> J.K.		<b>DATE</b> 8/25/04		<b>SIZE</b> A		<b>FSCM NO.</b> 55335		<b>DRAWING NO.</b> GLASS WEDGE BASE T-1 1/2	
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED				<b>SCALE</b> NONE		<b>RELEASED DATE</b> 5/5/00		<b>REVISION DATE</b> 8/25/04		<b>REV. NO.</b> A		<b>SHEET</b> 1 OF 1			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[E37](#) [E73](#) [E74](#) [E85](#) [E21203A](#)