



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
6835	5.0	.060	.050	0.63	100,000	C-8
7135	5.0	.075	.090	1.13	25,000	C-8
7155	5.0	.115	.150	1.89	40,000	C-8

METRIC 	DIMENSIONS ARE IN MILLIMETERS	JKL COMPONENTS CORPORATION TITLE T- 3/4 STANDARD AXIAL LEAD LAMP						
	TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0							
THIRD ANGLE PROJECTION	DRAWN BY L. WENGSTROM	APPV'D BY Q.C.	DATE 10/11/00	SIZE A	FSCM NO. 55335	DRAWING NO.	AXIAL STANDARD T-3/4	
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE NONE	RELEASED DATE 10/11/00	REVISION DATE	REV. NO.	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[7155](#)