


REV.	DESCRIPTION/ECO NO.	DATE
	RELEASED	10/11/00



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
6834	5.0	.060	.050	0.63	100,000	C-8
7134	5.0	.075	.090	1.13	25,000	C-8
7154	5.0	.115	.150	1.89	40,000	C-8

METRIC	DIMENSIONS ARE IN MILLIMETERS	JKL COMPONENTS CORPORATION			
	THIRD ANGLE PROJECTION	TITLE			
		T-1 STANDARD AXIAL LEAD LAMP			
		TOLERANCE UNLESS OTHERWISE SPECIFIED			
		1 PL +/- 0.2			
		2 PL +/- 0.20			
		ANGLE +/- 0			
DRAWN BY	APPR'D BY	DATE	SIZE	FROM NO.	DRAWING NO.
L. WENGSTROM	Q.C.	10/11/00	A	55335	AXIAL STANDARD T-1
- CAD DRAWING -					
MANUAL REVISIONS NOT PERMITTED					
SCALE		NONE	RELEASED	DATE	REV. NO.
			10/11/00		1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[6834](#) [7134](#)