




Rating	3A 125VAC 1.5A 250VAC		Mounting Hole	LED Rating Red:If=20mA,Vf=1.7V 
Contact Resistance	50m ohm Max.			
Insulation Resistance	DC 500V 100M ohm Min.			
Dielectric Strength	AC 1000V 1 minute			
Operation Temperature	-0°C ~ 65°C			
Switch Function	4P SPST ON-OFF (LED independent)			



***MATERIAL:**





Frame: Black, Nylon 66 (94-V2)

Actuator: Red, PC (94-V2)

Terminals: Silver plated, Copper alloy

Contacts: Silver plated, Copper alloy

Printed: None



C8\R13\R13-548BL-05(1830811)

Date	Name	Description							NO
Drawn	Checked	Approved	SCI BOM No.	1830811	Model Name	PUSH SWITCH			
曹 盈 芳	王 佰 山	李 景 煌	Customer No.	112-R13-548BL-BRR	Model No.	R13-548BL-05			REV.
02/17/'09	02/18/'09	02/19/'09	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.				0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[R13-548BL-05-BRR](#)