



Size No.		Screw Size		d		D		L		No. of Teeth	
Internal	External	mm	inch	Basic	Tol.	Basic	Tol.	Basic	Tol.	Internal	External
5	5	5	-	6.3	+0.2	10	-0.4	0.6	±.04	8	10
6	6	6	-	6.4	+0.3	12	-0.5	0.6	±.04	9	12
7	-	7	-	7.4	+0.3	13	-0.5	0.8	±.05	10	-
8	8	8	-	8.4	+0.3	16	-0.5	0.8	±.05	9	12
10	10	10	-	10.5	+0.4	18	-0.5	0.9	±.05	9	12
12	12	12	-	12.5	+0.4	21	-0.6	1	±.055	10	12

MATERIALS	
Style:	Internal tooth
Material:	Carbon spring steel
Hardness:	HRC40-50
Finish:	Zinc plating, chromate dip

Mouser Stock No.	Size (mm)
481-0685	5
481-0686	6
481-0687	7
481-0688	8
481-0680	10
481-0682	12

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eagle Plastic Devices:

[481-0687](#) [481-0682](#) [481-0688](#) [481-0685](#) [481-0686](#) [481-0680](#)