



Dimensions: mm (in.)

SPECIFICATIONS	
Insulation Resistance:	500VDC, 100MΩ min.
Voltage Breakdown:	1500VAC, 1 minute
Rating:	15A 125V/10A 250VAC
Body:	PBT 30% GF
Terminals:	Brass Nickel Plated
RoHS Compliant	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eagle Plastic Devices:](#)

[441-R345B-GR](#)