


R13-447



Rating
16(4)A 250V AC (A,N,R)
12(4)A 250V AC (C,D,G,H,I)
Contact resistance
50mΩ Max
Insulation resistance
DC 500V 100MΩ Min
Dielectric strength
AC 1500V 1 minute
Cut-out
 6 mm max

FEATURES

- * MATERIAL: Metal lever is nickel plated metal. Bushing is nylon with glass fiber (UL flame: 94V-0). Frame is nylon (UL flame: 94V-2).
- * Watertight boot (W-72) is optional for lever #1 only.

R13-447

FUNCTION		LEVER	TERMINAL
A 	H 	1 Metal Lever 	0 1 .250" SQ
			0 5 SO
C 	I 	3 Plastic Lever 	0 8 SC 6-32UNC
			1 2 SO
D 	N 		
G 	R 		

* () =momentary



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[R13-447A1-01](#) [R13-447C1-01](#) [R13-447D1-01](#) [R13-447R1-01](#)