



Rating	10A
Insulation Resistance	DC 500V 100M ohm Min.
Voltage Breakdown	AC 500V 1 minute
Operation Temperature	-20°C~80°C
Color	Black

Material:
Metal Clip: nickel plated SPCC
Plastic Cover: PVC , Black

*.Clamping force 2.5kgf at 8 mm(A)

*.Clamping force 300g±50g when clamped 12 AWG wire



Tolerances Unless Otherwise Specified ± 0.5

									△
									△
Date	Name		Description						NO
Drawn	Checked	Approved	SCI BOM No.	153010Z	Model Name	ALLIGATOR CLIPS			
林明呈			Customer No.	112-R8-91-B	Model No.	R8-91-B			Rev.
5/16/19			Unit	mm	Shin Chin Industrial Co., Ltd.				0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[R8-91-B](#)