







6 Pin, Vertical, Thru-Hole Receptacle

154-FWS20-E



6 Pin, Vertical, Thru-Hole Receptacle



PCB Footprint for Receptacle

Dimensions: In.

SPECIFICATIONS	
Type:	6 pin - 6 position
PC Board Thickness:	1.57mm recommended
Panel Thickness:	2.87mm max., if receptacle connector is mounted behind a panel
Housing Material:	PBT, LCP
Shell Plating:	Cu + N1, bright tin
Contact Plating:	2) 5μ" Au (L = 2.68mm); 5) 30μ" Au (L = 2.69mm); 6) 2μ" Au / PD-Ni 30μ" (L = 2.69mm); 7) 5μ" Au (L = 3.18mm) 8) 30μ" Au (L = 3.18mm)
RoHS Compliant	

Date Last Revised: 7-27-07

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-300997

154-FWS20-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-FWS20-E](#)