



## **Camera Plug**


161-RB011-EX


Date Last Revised: 8/8/19


## **DIMENSIONS: mm**











## **SPECIFICATIONS:**

• Rating: 0.5A/30VDC

• Contact Resistance : 20mΩ MAX.

Insulation Resistance : 100VDC 100MΩ MIN.
Dielectric Strength : 150VAC For 1 Minute.
Synthesized Inserting Strength : 4.0kg MAX.
Synthesized Pulling Strength : 0.3~ 3.5kg.

• Body Material: Nylon 94V - 0~2.

Note: RoHS Compliant by Exemption

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn: 161-RB011-EX