


DIMENSIONS: mm



Pin Hole Layout
(Jack Bottom View)

SPECIFICATIONS :

- Contact Resistance : 30mΩ max
- Current Rating : Max 5A, 24VDC
- Insulation Resistance : 100MΩ min at 500VDC
- Dielectric Withstand Voltage : 500VAC for one minute

Note: RoHS Compliant by Exemption

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301492

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[163-441CS-EX](#)