


Dimensions: mm (In.)



POS. 1	POS. 2	POS. 3
ON	OFF	ON
2-3	OPEN	2-1
 Comm. 2-3		 Comm. 2-1

Mechanical Specifications:

- Mechanical Life: 50,000 make-and-break cycles.
- Operating Temperature: -30°C to 85°C

Note:

- RoHS compliant by exemption

Electrical Specifications:

- Rating: 0.4A (VA) max./ 20V max. (AC or DC)
- Contact Resistance: 20mΩ max. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩ min.
- Dielectric Strength: 1,000 V RMS @ sea level

Materials:

- Case & Bushing: glass filled nylon 6/6, retardant, heat stabilized
- Actuator: nylon, black std. internal o-ring seal standard with all actuators
- Switch Support: brass or steel, tin plated.
- Terminals / Contact: gold plated with tin-lead

Sealed Sub-Miniature Rocker Switch (SMT)

103-7032-EVX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-7032-EVX](#)