





## Dimensions: mm (in.)

**P.C. Mounting**

POS.1	POS.2
ON	ON
2-3	2-1

**Switch Function****Electrical Specifications:**

- Contact resistance: 10mΩ max. initial @ 2-4VDC 100mA
- Insulation resistance: 1,000MΩ min.
- Dielectric strength: 1,000 V RMS@sea level
- Rating: 2A / 250VAC; 5A / 120VAC or 28VDC

**Mechanical Specifications:**

- Mechanical life: 30,000 make-and-break cycles
- Operating temperature: -30°C to 85°C

**Soldering Process:**

- Manual Soldering: Use soldering iron of 30 watts, controlled at 350°C approximately 5 sec. while applying solder.
- Wave Soldering: Recommended Soldering Temperature: 260±5°C  
Duration of Solder Immersion: 5±1sec. (PCB is 1.6mm in thickness)

**Note:**

- RoHS Compliant by Exemption

**Sealed Miniature Toggle Switch**  
108-1AS1T1693-EVX

**Mountain**  
**Switch**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

108-1AS1T1693-EVX