






Dimensions:mm (In.)

**Electrical Specifications:**

- Rating: 50mA/12VDC
- Life: 500,000 cycles
- Contact resistance: 100mΩ max.
- Insulation resistance: 100MΩ min. @ 500VDC
- Dielectric Strength: 250VAC for 1 minute

Mechanical Specifications:

- Type: SPST
- Operating force: 160±50g
- Operating temperature: -25°~+70°C
- Storage temperature: -30°~+80°C
- Travel: .01+.008-.004" (.25+.02-.1mm)

Materials:

- Cover: tin plated steel
- Contacts: silver clad phosphor bronze
- Terminals: silver clad brass
- Base: nylon, brown
- Stem: nylon, brown

Note:

- RoHS Compliant and process compatible with 260° solder

Tactile Switch (SMT)
101-0664-EV

**Mountain
Switch**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[101-0664-EV](#) [101-0664TR-EV](#)