



Dimensions: mm (In)

Mechanical Specifications:

- Operation Force: 260 ± 50gf
- Stroke: 0.30 + 0.1 mm/- 0.15 mm
- Operation Temperature: -25°C to +70°C
- Storage Temperature: -30°C to +80°C

Electrical Specifications:

- Electrical Life: 100,000 cycles min. for PT(C)L, PT(C)F
- Rating: 50mA, 12VDC
- Contact Resistance: 100mΩ max.
- Insulation Resistance: 100MΩ min. 500VDC
- Dielectric Strength: 250VAC/ minute
- Contact Arrangement: SPST

Materials:

- Cover: Stainless steel
- Contact disc: Stainless with silver cladding
- Terminal: Brass with silver plating
- Base: LCP High-temp thermoplastic; Color: Black
- Stem: LCP High-temp thermoplastic; Color: Black
- Adhesive Tape: Teflon

Note:

- RoHS compliant and process compatible with 260° solder.

Tactile Switch
101-TS4922R2600-EV

**Mountain
Switch**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-TS4922R2600-EV](#)