

Technical drawings of a 10-48 UNS nut assembly, showing dimensions in inches and millimeters.

Top View (Left):

- Outer Diameter: 8.13 (.32)
- Inner Diameter: 6 (ø.236)
- Width: 4.40 (.173)
- Hole Diameter: 9.14 (.36)

Side View (Top Right):

- Thread: 10-48 UNS
- Length: 8.30 (.327)
- Gap: .51 (.02)
- Height: 2.54 (.10)
- Distance: 3.30 (.13)
- Distance: 5.59 (.22)
- Distance: 9.40 (.37)
- Hole Diameter: 6 (ø.10)





Top View (Bottom Left): Without locking ring.

- Outer Diameter: 4.95 (ø1.95)
- Width: 4.55 (.179)
- Hole Diameter: 2.38 (ø.094)

Top View (Bottom Right): With standard locking ring.

- Distance: 5.08 (.20)
- Distance: 2.54 (.10)
- Distance: 6.10 (.24)
- Outer Diameter: 4.95 (ø1.95)
- Hole Diameter: 2.38 (ø.094)
- Hole Diameter: 1.09 (ø.043)

P.C. MOUNTING

POS.1	POS.2
	
ON	ON
2-3, 5-6	2-1, 5-4
	

Materials:

- Case: Diallyl phthalate (DAP)
- Acuator: Brass, chrome plated.
- Bushing: Brass, nickel plated.
- Housing: Stainless steel.
- Switch Support: Brass, tin plated.
- Terminal/Contact: Brass, silver plated.

- RoHS Compliant by Exemption

Mountain Switch

www.mouser.com 1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[108-2MD1T1B1M2QE-EVX](#)