


Dimensions: mm (In.)



Cutout	Circuit Arrangement
2.10 (.083) $\phi 26.70$ ($\phi 1.05$) $\phi 27.60$ ($\phi 1.08$) 3mm (.118) max	6P DPDT TERMINAL .187" SQ

Electrical Specifications:

- Rating: 8A / 125VAC / 250VAC
- Contact Resistance: 50m Ω max.
- Insulation Resistance: 500VDC 100M Ω min.
- Dielectric Strength: 1500VAC 1 minute

Note:

- RoHS Compliant

Rocker Switch
103-R13-245D-02-EV

**Mountain
Switch**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-R13-245D-02-EV](#)